


Matches ReiCatino®Line



ReiCatino® 100

Probat P 01
Giesen W1
Petroncini TT 5/ TT 10
Toper 3*
Typhoon 5*
Stronghold S7
Diedrich IR 1

ReiCatino® 450

Probat P 05 / P 12 / UG 15
Giesen W6 / W15
Petroncini TT 15 / TT 20
CoffeeTech Ghibli 15
Toper 5 / 10 / 15
Joper 5/ 15/ 25*
Coffed 3/ 5/ 15/ 25
Typhoon 20
Diedrich IR 2.5/ IR 5 / CR 25*/ DR 25
Stronghold S8 / S9

ReiCatino® 600

Probat UG 22 / P 25
Giesen W30
Petroncini 25
Coffeed 25
Genio 15*
Diedrich IR 12 / IR 25 / CR 25* / DR 35*
Toper 30
Joper 25 / 30

Please note: the matches are based on experience. The actual matching catalyst depends on the roasting exhaust air volume of each individual roaster and the temperature after the cyclone.

www.reicat-coffee.com